# Rainin QuickFlow Portable Easy-to-Use Aspirator

#### Smart features

- Variable speed settings
- Non-contact liquid level sensor
- 4L waste reservoir with carry handle
- Quick-snap connectors and tubing
- Autoclavable bottle and cap
- · Fits in most hoods
- Single channel, 8-channel and serological adapters

#### Guaranteed safety

The robust, non-contact liquid level sensor prevents overflows with auto-stop, a flashing light and audible alarm when the reservoir is full. Simple, self-sealing snap connectors keep the contents and any contamination inside the bottle.

	CATALOG No.	DESCRIPTION
	30519826	QuickFlow System – UNV Includes variable speed vacuum system, 4L autoclavable reservoir with inlet/outlet snap connector cap, non-contact liquid level sensor system for reservoir, inlet and outlet vacuum tubing with snap connectors and complete handle kit.
	30551530	QuickFlow System – LTS Includes variable speed vacuum system, 4L autoclavable reservoir with inlet/outlet snap connector cap, non-contact liquid level sensor system for reservoir, inlet and outlet vacuum tubing with snap connectors and complete handle kit.
C RAININGLIGHROW	30519824	QuickFlow Handle Kit – UNV Standard UNV kit includes ergonomic handle with conti- nuous and non-continuous flow control, three adaptors (8-channel/universal tip, single- channel/universal tip, single Pasteur pipette), vacuum tubing and handle hook accessory.
	30551534	QuickFlow Handle Kit – LTS LTS kit includes ergonomic handle with continuous and non-continuous flow control, three adaptors (8-channel/ universal tip, single- channel/universal tip, single Pasteur pipette), vacuum tubing and handle hook accessory.



# **Upgrade Your Liquid Aspiration – It's Easy!**

The Rainin QuickFlow Handle Kit – with three adapters – attaches easily to your central vacuum system



#### No-clog design

Unique channel design prevents blockage and delivers long-lasting performance.

#### Upgrade your system

QuickFlow handle and tubing attaches easily to your vacuum system.

### Hand-saving ergonomic design

Convenient, low-force tip ejection with one hand.

### Easy cleaning

The QuickFlow handle, adapters and tube is easy to clean and autoclavable.